

COAXIAL ADAPTER, BNC - A, X Ohm, plug / jack (male / female)

33_BNC-A-0-1/0--_ _

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
BNC	plug (male)	IEC 61169-8_MIL-STD-348A/301_CEECC 22120
A	jack (female)	HUBER+SUHNER-A

Interface and material data

BNC		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
A		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Insulator	PFA / PTFE	

Electrical data

Interface frequency	4 GHz
---------------------	-------

Mechanical data

Weight	0.0192 kg
Mating cycles	500

Environmental data

Operation temperature	-20 °C ... 85 °C
-----------------------	------------------

COAXIAL ADAPTER, BNC - A, X Ohm, plug / jack (male / female)
33_BNC-A-0-1/0--_--

Ordering Information Table		
Item number	Item description	Packaging type
22540589	33_BNC-A-0-1/0--_--E	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2252 / Date of publication: 12.04.2024 / uncontrolled copy