



Part Number : 936014682
Product Description : GWconnect STD - Standard, Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7908.6640.1



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect STD - Standard, Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black
Component Type	Single Lever Hood
IP Rating	IP66, IP67
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842370

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Cable Diameter	8.00-14.00mm
Component Size	«32X13»
Entry Location	Side
Gland Color	Black RAL 9005
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Hood	Polyamide
Material - Peg	Polyamide
Net Weight	36.000/g

Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts