

Part Number : 1122171024

Product Description : Woodhead ArcArrest
Plug with Handle, Drawplates, and Cap,
Switch-Rated, 60.0A, 480V AC, 3-Pole+Ground,
Insulator Keying Position 4, Three Grommets
Included

Series Number : 112217

Status : New Business Not Supported

Product Category : Wiring Devices

Engineering Number : ARC60MHDE03



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Wiring Devices
Series	112217
Description	Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 60.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included
IP Rating	IP69K
NEMA Configuration	N/A
Product Family	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Specialty	Switch-Rated
Type	Plug
UPC	78172558660

Agency

UL	E145922
----	---------

Electrical

Current - Maximum per Contact	60.0A
GFCI	No
Voltage - Maximum	480V AC

Physical

Cord Grip Body Size	F5 1 1/4"
Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Male
Length	178.99mm (7.047")
Lighted Connector	No
Locking Blade	N/A
Net Weight	1.000/g

Poles	3
Receptacle Type	N/A
Wire Size (AWG)	4 to 8

This document was generated on Oct 14, 2024