





Views from "X" rotated



Cable Diameter
7 - 12 mm

Cable Diameter
11 - 17 mm



	Cable Diameter	Solder Contacts	Crimp Contacts	Without Contacts
6 Pole	3 – 7mm	-	-	-
	7 – 12mm	-	-	-
	11 – 17mm	-	KAS6S01-409 1202300067	-
	Crimp range*		0,75-2,5mm²	
7 Pole	3 – 7mm	-	-	-
	7 – 12mm	KAS7S01-555 1202300070	KAS7S01-405 1202300072	-
	11 – 17mm	-	-	-
	Crimp range*		0,75-2,5mm²	
12 Pole	3 – 7mm	-	-	-
	7 – 12mm	KASCS01-555 1202300082	-	-
	11 – 17mm	-	-	-
	Crimp range*		0,34-1,0mm²	
17 Pole	3 – 7mm	-	-	-
	7 – 12mm	-	KASJS01-025 1202300096	-
	11 – 17mm	-	-	-
	Crimp range*		0,34-1,0mm²	
19 Pole	3 – 7mm	-	-	-
	(16+3)	-	KASLS01-225 1202300102	-
	11 – 17mm	-	-	-
	Crimp range*		0,34-1,0mm²/0,56-1,0mm²	

*Crimp range only applies to "Crimp Contacts" version

Notes:
Tolerances (unless specified): DIN ISO 2768 m

FUNCTIONAL SYMBOLS $\frac{F}{A}=0$ $\frac{F}{C}=0$ $\frac{F}{E}=0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#512581.			molex					
	MM		NTS										
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 753973 DRWN: LIKITV 2023/08/21 CHK'D: ANIKES1 2023/08/30 APPR: GGA 2023/08/31			M23 FA CABLE CONNECTOR FEMALE 90 DEG					
		mm	INCH										
	4 PLACES		±----		±----		PRODUCT CUSTOMER DRAWING						
	3 PLACES		±----		±----								
	2 PLACES		±0.05		±----								
	1 PLACE		±0.1		±----								
	0 PLACES		±----		±----		DOCUMENT NUMBER			DOC TYPE		DOC PART	REVISION
ANGULAR TOL ± ---- °		APPR: JKOLB		INITIAL REVISION: DRWN: BBRAUCH 2008/11/12 2009/03/02			SD-120230-002			PSD	001	A	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A3-SIZE	SERIES 120230	MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1	