





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	7723	RELEASED	5/31/05	
A	7723	UPDATED DRAWING	3/8/16	HR



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Gold flash over Nickel underplate overall
Electrical:
Current rating: 3 Amps max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant



Positions: 02 thru 40

A = .100 [2.54] x No. of Positions + .020 [0.50]

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	5/31/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.100 [2.54] SINGLE ROW RECEPTACLE STRIP
.335 [8.50] HEIGHT

SIZE X	PART NO. RS1-XX-G	REV. A
-----------	----------------------	-----------

REF: S00059T	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RS1-03-G](#) [RS1-05-G](#) [RS1-08-G](#) [RS1-12-G](#) [RS1-02-G](#) [RS1-06-G](#) [RS1-11-G](#) [RS1-04-G](#) [RS1-10-G](#) [RS1-09-G](#)
[RS1-07-G](#)