


# EXP-A921/05/P Datasheet

**Product Name // Inline Cable Connector Large Cable EXP-A921 Series 5 Contact Plug 20mm-22mm Cable (Yellow Gland)**

[View Product Page](#)



## // Product Description:

- ⊗ Inline Cable Connectors for hazardous areas
- ⊗ Water and dustproof to IP68 when mated with compatible connector
- ⊗ Positive fast-acting locking ring - can be turned with a gloved hand
- ⊗ Plug or Socket
- ⊗ 2, 3, 4, 5, 7, 10 Contact with leading Earth on 3, 4, 5, 7 Contact versions, trailing Neutral on 5 Contact version
- ⊗ Screw Terminals
- ⊗ Choice of cable acceptance 7mm-22mm diameter depending on part code (see data for details):
- ⊗ EXP-09 part codes 7mm-15mm diameter
- ⊗ EXP-A9 part codes (large cable version with strain relief clamp) 14mm-22mm diameter
- ⊗ Packs of Cable Glands for differing cable diameters available separately (EXP-0980, EXP-A980)
- ⊗ EXP-0991 heavy duty Sealing Cap available separately to maintain IP rating of unmated connectors
- ⊗ Mate with EXP-09 or EXP-A9 Series Flex and Panel Mount Connectors, as appropriate

## // General Information:

Product Display Title:	Inline Cable Connectors for hazardous areas
Product Family:	Circular Power Connectors
Product Series:	EXPlora
Approvals:	UL
Body Material:	Polyester (PET)
Body Material Type:	Plastic Body
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	18A
Diameter Over Coupling Ring Mm:	58mm
Flamability Rating:	UL94V-0
Function:	Inline Cable Connector
Ip Rating:	IP68
Max Cable Entry Size:	22mm
Min Cable Entry Size:	20mm
Max Contact Accomodation Awg:	14AWG
Min Contact Accomodation Awg:	10AWG
Max Contact Accomodation Mm2:	4mm <sup>2</sup>
Min Contact Accomodation Mm2:	2.5mm <sup>2</sup>
Max Operating Temperature:	+55°C
Min Operating Temperature:	-20°C
Number Of Contacts:	5 Contacts
Voltage Max:	600V

### // Product PDF Links

[EXP-lora Series power connectors...](#)

### // Product 3D CAD Model Links

[EXP-A921/05/P3D CAD Model](#)



Have a question or project enquiry you'd like to talk to us about?

[Click Here To Contact Us](#)