






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		新开模具, 参照实物修正图纸	2024.9.24	桑葚




3D VIEW



Recommend of PC Board Holes
Tolerance : ±0.05(Printed-Top view)

规格 Specifications:
额定电压 Voltage rating:12 VAC/DC。
额定电流 Current rating:2A AC/DC
绝缘电阻 Insulation resistance:≥100MΩ Min
接触电阻 Contact resistance:≤50mΩ Max
耐电压 Withstanding voltage:500V AC/minute
寿命 DURABILITY: 5000 CYCLES MIN
拔出力 CONNECTOR MATING FORCES: 3~30N
插入力 CONNECTOR UNMATING FORCES: 3~30N
温度区间 Temperature range:-20℃to+70℃



PART NO.	φPIN
DC-045B-1.3-SMT	φ1.30
DC-045B-1.0-SMT	φ1.00

⑥	HOUSING	1	PA9T	Black	AuGLAR	±5°
⑤	CEN PIN	1	H65	Ni-Plated		
④	TERMINAL 4#	1	C2680 t=0.25	Ag-Plated		
③	TERMINAL 3#	1	C2680 t=0.25	Ag-Plated		
②	TERMINAL 2#	1	SUS301 t=0.30	Ag-Plated		
①	TERMINAL 1#	1	C2680 t=0.25	Ag-Plated		
No.	PART NAME	QTY	MATERIAL(THICK)	PLATING(COLOR)	UNSPECIFIED TOLERAUCES	
www.helloxkb.com				www.helloxkb.cn	www.xk-dg.cn	



DESIGN	桑葚	VIEW:	MODEL TYPE: DC POWER JACK
CHECKED		UNIT: mm/in	PART NO.: DC-045B-X-SMT
APPROVED		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE N/A
			PAGE 1/1
			REVISION A1