

## Single-Gang European-Style Gang Frame for Insert Modules, White, TAA

MODEL NUMBER: **N042E-WF1**



European-style gang frame accepts compatible inserts for terminating premise audio/video, voice or data applications.

### Features

#### European Gang Frame Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This European-style outlet gang frame for mounting and trunking is ideal for terminating your premise wiring applications, including home theater, VoIP phones and Ethernet. The N042E-WF1 protects electrical and network cables to help prevent accidental damage to your application. It's compatible with N042E-Series European unloaded modules and blank insert (sold separately).

#### High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white plastic cover plate measures 81 x 81 x 15 millimeters (outer frame) and 45 x 45 millimeters (inner frame). It helps hide unattractive cabling and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

### Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Helps prevent accidental cable damage and hides unattractive wiring
- Compatible with N042E-Series European modules and inserts
- High-impact plastic construction designed to blend in with your home/office décor

### Package Includes

N042E-WF1 Single-Gang Europe-Style Gang Frame, White

## Specifications

OVERVIEW	
UPC Code	037332268853
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB 2.0 (High Speed)
Country/Region	Europe
PHYSICAL	
Color	White
Material of Construction	ABS
Total Number of Ports	0



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / in.)	1.770 x 1.770 x 0.590
Finish	Matte
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Snagless Connector	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.