

## Harax PG 13,5/ panel feed through / 3-po



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 130 1023
Specification	Harax PG 13,5/ panel feed through / 3-po
HARTING eCatalogue	<a href="https://b2b.harting.com/21011301023">https://b2b.harting.com/21011301023</a>

### Identification

Category	Connectors
Series	HARAX®
Element	Panel feed through
Specification	With solder termination for front mounting

### Version

Termination method	HARAX® connection technology
Shielding	Unshielded
Number of contacts	3

### Technical characteristics

Conductor cross-section	0.75 ... 1.5 mm <sup>2</sup>
Conductor cross-section	AWG 18 ... AWG 16
Wire outer diameter	≤2.8 mm
Rated current	16 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	>10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ

## Technical characteristics

Limiting temperature -25 ... +85 °C

Degree of protection acc. to IEC 60529 IP67

Size Pg 13.5

Cable diameter 6 ... 9 mm

Isolation group I (600 ≤ CTI)

## Material properties

Material (insert) Polyamide (PA)  
Thermoplastic polyurethane (TPU)

Material (contacts) Copper alloy

Surface (contacts) Gold plated

Material (hood/housing) Polyamide (PA)  
Thermoplastic polyurethane (TPU)

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances Not contained

REACH ANNEX XIV substances Not contained

REACH SVHC substances Not contained

California Proposition 65 substances Yes

California Proposition 65 substances Nickel  
Naphthalene

## Specifications and approvals

UL / CSA UL 1977 ECBT2.E102079  
CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size 1

Net weight 24.25 g

Country of origin Germany

European customs tariff number 85366990

GTIN 5713140136748

eCl@ss 27440103 Sensor-actuator connector chassis (sensor technology actuator)