



製品レイアウト
PRODUCT LAYOUT

コネクタ外形
CONNECTOR OUTLINE





基板レイアウト(参考)

PCB PATTERN LAYOUT (REFERENCE)
(参考: メタルマスク厚さ 0.10mm, マスク開口率100%)
(REFERENCE: METAL MASK THICKNESS 0.10mm, APERTURE RATIO 100%)




パターン非推奨エリア

パターンを引き回す際は、製品機能に影響がないことをご確認ください。
PATTERN IS NOT RECCOMENDED ON THE HATCHED AREA.
PLEASE CHECK NOT TO HAVE PROBLEM FOR PRODUCT FUNCTION
WHEN SETTING PATTERN ON THE HATCHED AREA.







嵌合相手: 502578 シリーズ
MATE WITH: 502578 SERIES

MATED CONNECTORS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex CLIK-MATE 1.5 SINGLE ROW SMT VT TYPE REC ASSY GOLD PLATING				
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
ANGULAR TOL ± 3.0 °			EC NO: 742719 DRWN: MIKEDA01 2023/06/23 CHK'D: SAKIYAMA 2023/06/23 APPR: AIDA 2023/06/23				PRODUCT CUSTOMER DRAWING				
4 PLACES ± 0.2											
3 PLACES ± 0.2											
2 PLACES ± 0.2											
1 PLACE ± 0.2											
0 PLACES ± 0.2			INITIAL REVISION: DRWN: MIKEDA01 2019/11/07 APPR: KOMURAKAMI 2019/11/20				DOCUMENT NUMBER 2132250000-SD		DOC TYPE PSD	DOC PART 000	REVISION F
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION 		DRAWING A3-SIZE	SERIES 213225	MATERIAL NUMBER		CUSTOMER GENERAL		SHEET NUMBER 2 OF 6

ロック形状および吸着エリア
LOCK SHAPE AND VACCUME AREA




SECTION X-X

12-15 極
12-15 CKTS

5.0	15
	14
	13
	12
	11
	10
	9
	8
13.6	7
12.1	6
10.6	5
9.1	4
7.6	3
6.1	2
D	極数 CKT NO

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
CURRENT REV DESC:	
molex	
CLIK-MATE 1.5 SINGLE ROW SMT VT TYPE REC ASSY GOLD PLATING	
PRODUCT CUSTOMER DRAWING	
DOCUMENT NUMBER: 2132250000-SD	
DOC TYPE: PSD	
DOC PART: 000	
REVISION: F	
SHEET NUMBER: 3 OF 6	



NOTES					
5. 梱包数量 : 900個/リール NUMBER OF CONNECTORS : 900 PIECES/REEL					
6. リードテープ長さ LEAD TAPE LENGTH					
引き出し方向 PULL OUT DIRECTION 部品挿入部 COMPONENT SUPPLIER 末端部(空部) TAIL PART (EMPTY) 100 MIN. 400 MIN. トップテープ接着部(空エンボス) 20 PIECES MIN. TOP TAPE BONDED PART(EMPTY)					
7. トップテープの剥離強度はJIS C0806-3に準拠。 TOP TAPE PEELING FORCE IS DEFINED BY JIS C0806-3.					
8. 本製品は乾燥剤入り、ハイバリア梱包である。 THIS PRODUCT IS DELIVERD IN HIGH BARRIER PACKAGE WITH DESICCANT.					
49.4	45.4	20.2	40.4	44±0.3	15
					14
					13
					12
					11
					10
37.4	33.4	14.2	28.4	32±0.3	9
					8
					7
					6
29.4	25.4	11.5	-	24 ^{+0.3} _{-0.1}	5
					4
					3
					2
J	H	G	F	エンボステープ幅E WIDTH OF TAPE	極数 CKT. NO.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex										
mm		NTS																
GENERAL TOLERANCES (UNLESS SPECIFIED)								EC NO: 742719 DRWN: MIKEDA01 2023/06/23 CHK'D: SAKIYAMA 2023/06/23 APPR: AIDA 2023/06/23										
ANGULAR TOL ± 3.0 °																		
4 PLACES		± 0.2		INITIAL REVISION: DRWN: MIKEDA01 2019/11/07 APPR: KOMURAKAMI 2019/11/20				DOCUMENT NUMBER			DOC TYPE		DOC PART		REVISION			
3 PLACES		± 0.2						2132250000-SD			PSD		000		F			
2 PLACES		± 0.2		THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER			SHEET NUMBER	
1 PLACE		± 0.2						A3-SIZE		213225				GENERAL			4 OF 6	
0 PLACES		± 0.2																
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																		
DRAWING		A3-SIZE		213225														
SERIES		213225																
MATERIAL NUMBER																		
CUSTOMER																		
SHEET NUMBER																		
4 OF 6																		
DOCUMENT STATUS		P1		RELEASE DATE		2023/06/23 10:36:34												

FORMAT: master-lb-prod-A3

