

BU-7044-B-XX-@

(Test Lead: Dual Stackable Banana Plug to Stackable 0.080" Pin Tip Probes)



- Mueller's BU-7044-B is a test lead with a dual, stackable 4mm banana plug to stackable, 0.080" (2mm) pin tip probes. Banana plugs are spaced 0.75" (19mm) center-to-center and mate with any standard, 4mm banana jacks.
- Constructed with RG-58/U coaxial cable. Center conductor is 20 AWG (19x33) tinned copper and the shield is tinned copper braid (95% coverage).
- Material:

Banana plugs	Nickel-plated phosphor bronze
Pin tips	Nickel-plated brass
Overmold	Polypropylene
- Rating:

Impedance	50 Ohms
Voltage	Hands-free testing to 500 VRMS
- Length: The "XX" in the part number represents overall length in inches.
Standard lengths: 12", 24", 36", 48", 60"
- Color: The "@" in the part number represents the color of the overmold material on the banana plug.
Available colors: -0 Black, -2 Red

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mueller Electric:](#)

[BU-7044-B-24-0](#) [BU-7044-B-12-0](#) [BU-7044-B-12-2](#) [BU-7044-B-24-2](#) [BU-7044-B-36-0](#) [BU-7044-B-36-2](#)