





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1670210/11	2016/07/12	Mafei	Updated The Recommended Panel Dim.






Recommended Panel
Cut-Out




AAD-XXPMMS-SS7001
02:2Pin
03:3Pin

With Liquid Glue



3 Pin



2 Pin

Pin Assignments Front View

- Note:
- * Ⓢ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * Gasket: Silicone, Gray.
 - * Use with waterproof cap or dust cap
Maximum Panel Thickness:3.3mm
 - * Use without waterproof cap or dust cap
Maximum Panel Thickness:4.5mm

UNIT:mm		TITLE MINI PANEL SCREW M CONN M PIN		ITEM NO		DRAWN BY Mafei		DATE 2016-07-12	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 2:1	SIZE A4	SHEET 1 OF 1	DWG NO AAD-XXPMMS-SS7001	CHECKED BY Youdan		DATE 2016-07-12	
REV. B		WC-REV. A.1	QC: Inspection item		CUSTOMER ALTW	APPROVED BY Jerry		DATE 2016-07-12	

Amphenol LTW
安費諾亮泰企業股份有限公司