


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
FAP6WFCZ	1.984 LB/10 PCS. (900 G/10 PCS.)


**NOTES:**

NOTE: 1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.  
2. PRELOADED WITH SIX FC MULTIMODE/SINGLE MODE THREADED ADAPTERS WITH CERAMIC SLEEVES.  
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.  
4. MATERIAL:  
PANFI ADAPTER HOUSING

## THREE      ABAL TER MOESTRE

CRS POWDER COATED

## METAL



**NOTE:** FRONT DUST COVERS REMOVED FOR CLARITY

								CADD FILENAME/LAYERS MO0852AM_DC_00A.prt			
								 <b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS			
								<b>FIBER OPTIC SIX PORT PANEL WITH FC CERAMIC CONNECTOR CUSTOMER DRAWING</b>			
								<b>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:</b> $(.X) \pm (.XX) \pm .010 (.3)$ $(.XX) \pm .03 (.8)$ <b>ANGLES <math>\pm</math></b>	<b>UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.</b>		
								DRAWN BY AFW  DATE 11-20-00  REV'D	MAT'L'S  SEE NOTES	SCALE <b>3 1/4</b>	
R	11-20-00	AFW	RELEASED TO PRODUCTION		00852-43						DRAWING NO. <b>00852-43</b>
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP		