



Pushing Performance  
Since 1945

# Frame Han 24HPR EasyCon H. sh. st. i



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 024 9951
Specification	Frame Han 24HPR EasyCon H. sh. st. i
HARTING eCatalogue	<a href="https://b2b.harting.com/09400249951">https://b2b.harting.com/09400249951</a>

## Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Frame
Description of the accessory	for standard inserts for Han-Modular® hinged frames

## Version

Gender	Male Female
Size	24 B
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	2x M4/M5 distance bolts (AF 7) 2x M5/M6 distance bolts (AF 7) 2x M4 screw 2x washer SK S4

## Technical characteristics

Tightening torque	1.5 Nm Fixing screws M4 6 Nm Distance bolt
Mating cycles	≤100

## Material properties

Material (accessories)	Stainless steel
RoHS	compliant
ELV status	compliant



Pushing Performance  
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	80 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140194281
ETIM	EC002310
eCl@ss	27440210 Fixing element for industrial connectors