

Double-Gang Surface Mounting Box, UK Style, 86 x 147 x 47 mm, White, TAA

MODEL NUMBER: N042U-MB2



Works with a compatible wall plate to complete in-wall audio/video, voice and Ethernet connections using any type of keystone jack.

Features

UK-Style Back Box Connects Audio/Video, Voice and Data Cable Lines in Your Network

This double-gang box combines with a compatible wall plate (sold separately) to complete a premise wiring application, such as home theater (audio/video), VoIP phone (voice) or Ethernet (data) network.

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This durable white mounting box blends elegantly into any home or office décor for a sleek, professional installation. Mounting screws are included. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

Compatible with U.K. Applications

The N042U-MB2 is designed to work with standard double-gang wall plates measuring 86 x 147 millimeters. Compatible models include N042U-WF2-2, N042U-WM1-S, N042U-WHM-S, N042U-WHM-SA and N042U-WF2-6C.

Highlights

- Ideal for completing home theater, VoIP or Ethernet wiring installations
- High-impact plastic construction designed to blend in with your home/office décor

Package Includes

- N042U-MB2 Double-Gang UK-Style Mounting Box, White
- (2) Mounting screws

Specifications

OVERVIEW	
UPC Code	037332269362
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); HDBaseT; HDMI; DisplayPort
Country/Region	UK
PHYSICAL	
Color	White
Material of Construction	ABS



Powering Business Worldwide

TRIPP LITE
SERIES

Total Number of Ports	0
Unit Dimensions (hwd / in.)	5.768 x 3.386 x 1.850
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94; UL Listed; cUL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.