


逻辑关系图 Logic

parameter table:

项目 Category	参数 Parameter	备注 Comments
板载额定电流 Current	0.8A	
端子接线规格 Terminal	Terminal spacing 5.0mm, wire size 18-26 AWG	
Screw Terminal Size	采用一字螺丝刀, 刀口不能大于2.5mm宽	
D-SUB Material	冲针+环保塑料 RoHS	
PCB Material	FR4	
Voltage	70V maximum between any two sinals	
temperature	-10℃ to 70℃	
Ambient Humidity	10% to 90% RH, NON-CONDENSING	

Draw	Hero. Xu	Date	2020-03-02	NAME	Terminal board	model	DB37-G2-01 螺母式
Auditing	Hero. Xu			Version	Ver:1.0	客户	
Approve						编号	
未注特性公差GB1804-m级 (单位:mm)				投影角度	图纸比例	第 1 张 共 1 张	
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2
							2.0
							角度公差 ±0.5°
							1:1
							中山市肯博电子科技有限公司 www.kingpow.cn