

USB 2.0 Adapter - USB-C to USB Micro-B (M/F)

MODEL NUMBER: U040-000-MIC-F



Connects your USB-C device to a USB-A host port using your existing USB Micro-B cable.

Description

The U040-000-MIC-F USB 2.0 Hi-Speed Adapter (M/F) allows you to connect an existing USB Micro-B cable between the USB-C port on your computer, laptop or tablet and a USB-A host port. This allows you to sync and charge your USB-C device without the extra expense of a new USB-C cable.

The portable, compact adapter supports USB 2.0 data transfer speeds up to 480 Mbps. The reversible USB-C male connector plugs into a USB-C port in either direction for fast, fumble-free connection every time.

Molded nickel-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. The U040-000-MIC-F is backward compatible with previous USB generations.

Features

Use Your Existing USB-C Device with an Existing USB Micro-B Cable

- Recommended for charging or synchronizing data on your USB-C computer, laptop or tablet
- Supports USB 2.0 data transfer speeds up to 480 Mbps
- Backward compatible with previous USB generations

Reversible USB-C Male Connector

- Fumble-free reversible plug connects in either direction to ensure fast, easy connection every time

Premium Construction

- Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss

Specifications

OVERVIEW	
UPC Code	037332205032
Technology	USB 2.0 (High Speed)

Highlights

- Supports data transfer speeds up to 480 Mbps
- Reversible USB-C plug provides fumble-free connection
- Gold-plated contacts for maximum conductivity and minimum data loss
- Backward compatible with previous USB generations

System Requirements

- USB-A host
- Device with USB-C female connector
- USB 2.0 Micro-B cable

Package Includes

- U040-000-MIC-F USB 2.0 Hi-Speed Adapter, USB-C to USB Micro-B (M/F)



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Connector Plating	Nickel
PHYSICAL	
Color	Gray
Material of Construction	Aluminum
Shipping Dimensions (hwd / in.)	2.76 x 1.57 x 0.50
Shipping Dimensions (hwd / cm)	7.01 x 3.99 x 1.27
Shipping Weight (lbs.)	0.01
Unit Dimensions (hwd / in.)	0.240 x 0.400 x 0.980
Unit Dimensions (hwd / cm)	7.01 x 3.99 x 1.27
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	5% to 95% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Certifications	EN 5035
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.