



Female



parameter table:

Num	Category	Describe
1	Max Current	0.7A
2	Cable gauge (AWG)	18-26 AWG
3	Terminal Pitch:	Pitch:5.0mm
4	PCB Material	FR4
5	D_SUB Withstanding voltage	300V AC/MINUTE
6	D_SUB Operating temperature	-20℃ to 105℃
7	Rated voltage according to	UL:
8	Rated current according to	UL:
9	D_SUB Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L165*W93*H53mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2019. 11. 29				名称	端子板		型号	DB25-M2-01	
审核							版本	Ver:1.0		客户		
核准										编号		
							投影角度		画板比例		第 1 张 共 1 张	
未注特性公差GB1804-m (单位:mm)									1:1		中山市肯博电子科技有限公司 www.kingpow.cn	
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000						
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2	2.0				