

# Keystone Jack Cat6/Cat5e, RJ45, Shuttered, Dust Cap - Toolless, PoE/PoE+ Compliant, White, TAA

MODEL NUMBER: N238-001-GY-TF



Toolless RJ45 keystone jack lets you terminate your Cat6/5e network patch cable without using a punchdown tool.

## Features

**Toolless Keystone Jack Strengthens Your High-Speed Cat5e/Cat6 Network** Terminate your network patch cable without the time, effort and expense of a punchdown tool. Ideal for Cat6 premise wiring, the RJ45 keystone jack snaps into wall plates, patch panels and surface-mount boxes and works with all shielded Cat6 cables. Toolless punchdown connection is compatible with 22–24 AWG solid wire cabling. A shutter/dust cap protects the jack from dust and other contaminants when not in use.

**Specifically Designed for Use in Surveillance, VoIP and Other PoE+ Applications** This PoE+ (Power over Ethernet) jack prevents spark-gap erosion that degrades the plug and jack contacts over time and can affect data and/or power transmission capabilities to maximize performance with PoE applications. The N238-001-GY-TF handles the frequent mating and unmating of surveillance cameras, VoIP phone systems, wireless access points and other PoE and PoE+ devices under electrical load.

**TAA-Compliant for GSA Schedule Purchases** The N238-001-GY-TF is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Specifications

OVERVIEW	
UPC Code	037332236197
Product Type	RJ45 Keystone Jack
Technology	Cat5/5e; Cat6
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)

## Highlights

- Keystone design compatible with wall plates, patch panels and surface-mount boxes
- RJ45 termination is quick and easy with no punchdown tools required
- PoE+ compliant jack is recommended for Cat6 premise wiring
- Specially designed to prevent spark-gap erosion that can affect transmission
- Includes shutter/dust cap to protect end from dust and debris when not in use

## Applications

- Connect a Cat5e/6 network with PoE+ devices mounted in areas that are difficult to reach or have no electrical outlets
- Set up indoor digital signage in offices, hotels, restaurants, bars, bus stations and airports

## Package Includes

- N238-001-GY-TF Keystone Jack Cat6/Cat5e, White, TAA
- Shutter/dust cap
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	110 IDC
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
<b>PHYSICAL</b>	
Color	White
Connector Color	White; Gray
Housing Color	White; Gray
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 5.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 13.97
Shipping Weight (lbs.)	0.02
Shipping Weight (kg)	0.01
Unit Dimensions (hwd / in.)	0.760 x 0.860 x 1.350
Unit Dimensions (hwd / cm)	1.92 x 2.19 x 3.43
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Relative Humidity	10% to 90% RH, Non-Condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N238-001-GY-TF](#)