








parameter table:

Num	Category	Describe
1	Max Current	0.8A
2	Cable gauge (AWG)	14-24 AWG
3	D SUB connector:	冲针头 Stamp Pin
4	PCB Material	FR4
5	D SUB Withstanding voltage	500V AC/MINUTE
6	D SUB Operating temperature	-20℃ to 105℃
7	Rated voltage according to	UL:No
8	Rated current according to	UL:No
9	D SUB Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L165*W95*H53mm /
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2021.07.02			名称	端子台	型号	DB50-G7
审核						版本	Ver:1.0	客户编号	
核准									
未注线性公差GB1804-m级 (单位:mm)						摄影角度	图纸比例	第 1 张 共 1 张	
尺寸	公差	3-6	6-30	30-120	120-400	400-1000	1000-2000	2000-4000	角度公差 ± 0.5 °
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2	2.0	
							1:1	中山市肯博电子科技有限公司 www.kingpow.cn	