

Datasheet for part number MKJ1A6Z16-12PA

Our Catalog Part Number: MKJ1A6Z16-12PA
Our Global Manufacturing Part Number: 155128-2501
Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJ1

Product Datasheet	
Series	Threaded Coupling, Double Start ACME Thread
Class	Environmental Plug and Receptacle with Banding/Overmolding Attachment
Shell Style	Straight Plug
Plating	Aluminum/Zinc Nickel, Black
Contact Arrangement	12 Size 16 Contacts
Gender	Pin, Crimp, Removable
Polarization	Normal (150° 210°)
Wire Accommodation	#16 - #20 AWG
Current Rating	13 Amps Maximum
Voltage Rating	1800 VAC RMS Sea Level
Insulator Resistance	5000 Megaohms Minimum
Operating Temperature	-55°/+150°
Contact Resistance	8 Milliohms Maximum
Vibration	20 g' in Accordance with MIL-STD-1344 Method 2005, Condition IV
Shock	300 g' (MKJ1) 50 g' (MKJ0 and MKJ4) in Accordance with MIL-STD-1344 Method 2004, Condition E
EMI Shielding Effectiveness	40dB Attenuation, 100 MHz to 1000 MHz