


parameter table:

Num	Category	Describe
1	Max Current	0.5A
2	Cable gauge (AWG)	18-26 AWG
3	DSUB Pitch:	Pitch:1.98*2.41mm
4	PCB Material	FR4
5	DSUB Withstanding voltage	300V AC/MINUTE
6	DSUB Operating temperature	-20°C to 105°C
7	Rated voltage according to	UL:
8	Rated current according to	UL:
9	SCSI Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L130*W130*H60mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2023.08.30	名称	端子台	型号	DB78-M7
审核				版本	Ver:1.0	客户编号	
核准				摄影角度		图纸比例	第 1 张 共 1 张
未注线性公差GB1804-m级 (单位:mm)				角度公差	±0.5°		
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2
						1:1	
				中山市肯博电子科技有限公司 www.kingpow.cn			