




Part Number : [936030049](#)
Product Description : GWconnect Connector Kit, 10 Pole, Series S-E Female-Male Inserts, Pg16 Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 10B «57x27», Grey
Series Number : 93603
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7910.6750.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Connectors
Series	93603
Description	GWconnect Connector Kit, 10 Pole, Series S-E Female-Male Inserts, Pg16 Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 10B «57x27», Grey
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
UPC	887191862736

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Physical

Color - Cable Jacket	N/A
Component Size	10B «57X27»
Lock to Mating Part	Yes
Mounting Style	Bulkhead
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Kit Component Parts

Description	Part Number
GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 10B «57x27», Extended Pg16 Thread, Grey	<u>0936011718</u>

GWconnect Screw Terminal Insert, Male, 10-Pole, 16A, with Wire Protection, Silver (Ag) Plated Contacts, Size 10B «57x27»	<u>0936010238</u>
GWconnect Screw Terminal Insert, Female, 10-Pole, 16A, with Wire Protection, Silver (Ag) Plated Contacts, Size 10B «57x27»	<u>0936010231</u>
GWconnect STD - Standard, Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 10B <<57x27>>, Pg16 Thread, Grey	<u>0936011537</u>