

**SPECIFICATIONS:**

**MATERIALS:**

HOUSING:	PBT, UL94 V-0, BLACK
CONTACTS:	GOLD PLATED BRASS (SEE PART NUMBER KEY)
NUT:	NICKEL PLATED AL
SHELL:	NICKEL PLATED AL
ORING:	EPDM
MAIN BODY:	NICKEL PLATED AL
GLAND:	SILICONE, BLACK
GLAND CAGE:	POM, WHITE
GLAND NUT:	NICKEL PLATED AL

**ELECTRICAL:**

RATED CURRENT:	4A
RATED VOLTAGE:	250V
INSULATION RESISTANCE:	100 MOhms MIN.
CONTACT RESISTANCE:	10 mOhms MAX.

**ENVIRONMENT:**




OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67

MAX WIRE AWG: 20

**NORCOMP MATING PART NUMBERS:**

- 858-003-103RKT4\*
- 858-R03-103RLU4\*
- 858-R03-103RSS4\*
- 859-R03-103R004\*
- 860-003-113R004\*
- 861-R03-113R004\*

\*Also all material and contact plating variants



**858-L03-203RKTY**

1 = GOLD FLASH  
4 = 10µ" GOLD

**RoHS COMPLIANT**

UNITS = inch [mm]

**DO NOT SCALE FROM DRAWING**



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
**M. SIGMON**

DATE:  
**03/07/2016**

**NorComp**

SCALE:  
NTS

SHEET 1 OF 1

REV 6

DWG NO.

**858-L03-203RKTY**