



Image for illustrative purpose only

Summary

[Request a quote](#)

Wire Size/AWG	24 - 22
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted

Technical details

Electrical Configuration

Rated current	8 A
Contact Type	Print (straight)
Number of differentiated pairs (High speed)	4
Wire Size/AWG	24 - 22

Form & Material

Shell style / Model id	PE - Fixed receptacle, nut fixing and mold stop
Socket / Receptacle	Fixed Panel Rear Mounted
Keying	3 keys (beta=130, gamma=100, plug: male contacts, receptacle: female contacts)
Colour	Grey

Environment

Environmental sealing (IP rating)	IP68
Temperature range	-20°C / +200°C

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	T type cable adapter

https://www.lemo.com/int_en/peu-2m-514-xlpt6.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.