



Male



parameter table:

Num	Category	Describe
1	Max Current	0.75A
2	Cable gauge (AWG)	18-26 AWG
3	Terminal Pitch:	Pitch:5.0mm
4	PCB Material	FR4
5	D SUB Withstanding voltage	300V AC/MINUTE
6	D SUB Operating temperature	-20℃ to 105℃
7	Rated voltage according to	UL:
8	Rated current according to	UL:
9	D SUB Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2020. 09. 04	名称	端子板	型号	DB15-G2-01 螺母式
审核				版本	Ver:1.0	客户编号	
核准				投影角度	图版比例	第 1 张	共 1 张
尺寸公差				角度公差	± 0.5 °	中山市肯博电子科技有限公司	
未注线性公差GB1804-m (单位mm)				1:1		www.kingpow.cn	
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2
							2.0