







DB26端子台




专业制造自动工控配件

Pin number



parameter table:

Num	Category	Describe
1	Max Current	0.5A
2	Cable gauge (AWG)	14-26 AWG
3	D_SUB connector:	冲针头 Pin
4	PCB Material	FR4
5	D_SUB Withstanding voltage	300V AC/MINUTE
6	D_SUB Operating temperature	-20℃ to 105℃
7	Rated voltage according to	UL:No
8	Rated current according to	UL:No
9	D_SUB Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L116*W95*H54mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2019. 11. 14	名称	端子台	型号	DB26-M7
审核				版本	Ver:1.0	客户编号	
核准				摄影角度	图纸比例	第 1 张 共 1 张	
未注线性公差GB1804-m级 (单位:mm)				角度公差	± 0.5 °	1: 1	
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2
							2.0
				中山市肯博电子科技有限公司		www.kingpow.cn	