








Pin number



parameter table:

Num	Category	Describe
1	Max Current	0.8A
2	Cable gauge (AWG)	14-26 AWG
3	IDC Pitch:	Pitch:2.54mm
4	PCB Material	FR4
5	IDC Withstanding voltage	300V AC/MINUTE
6	IDC Operating temperature	-20℃ to 105℃
7	Rated voltage according to	UL:E311899
8	Rated current according to	UL:E311899
9	IDC Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L130*W95*H54mm /
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2019. 10. 15	名称	端子台	型号	IDC40P-C
审核				版本	Ver:1.0	客户编号	
核准				摄影角度	图纸比例	第 1 张	共 1 张
未注线性公差GB1804-m级 (单位mm)				角度公差	± 0.5 °	1:1	
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2
							2.0
				中山市肯博电子科技有限公司		www.kingpow.cn	