


General information

Part number	K41F1C-P02LPH0-150S	
Termination	solder	
Size	1	
Locking principle	break, push	
Coding	1_halfshell	Illustrations may differ from original product. Dimensions, unless otherwise specified, in mm.
Cable Diameter	cable_mini_15	
Cable outlet	bend_relief	



Contact insert description

Number of contacts	2
Contact type	sockets
Contact diameter	13mm
Insulator material	peek
Wire cross section	20_awg
Termination	solder
Termination diameter	11mm

reverse gender on request

Technical information

Max. creepage and air clearance distance	13_mm	09_mm
Nominal current single contact	12_a	iec_60512_5_2
Nominal current insert	12_A	vde_0298_4
Test voltage	165_kv_ac	sae_13441
safety_text		

Mechanical and environmental data

Degree of protection*	ip68
Operating temperature	40_120_c
Mating cycles	5000

mated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2

ul_text

illustrative_text