



Part Number : 191600040

Product Description : Twist Lock Splice for 22-14 AWG Wire, Blue

Series Number : 19160

Status : Active

Product Category : Splices

Engineering Number : TL-B



---

## Documents & Resources

### Drawings

191600040\_sd.pdf

### Specifications

PS-19902-013-001.pdf

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Splices
Series	19160
Description	Twist Lock Splice for 22-14 AWG Wire, Blue
Product Family	Splices
Product Name	Closed-End Twist Lock
UPC	800753110441

#### Agency

CSA	LR700095
UL	E32244

#### Electrical

Voltage - Maximum	300V
-------------------	------

#### Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.710/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	7.11mm max.

Wire Size (AWG)	14, 16, 18, 20, 22
-----------------	--------------------

---

This document was generated on Oct 14, 2024