



parameter table:

Num	Category	Describe
1	Max Current	0.7A
2	Cable gauge (AWG)	14-24 AWG
3	D_SUB connector:	冲针头 Stamp Pin
4	PCB Material	FR4
5	D_SUB Withstanding voltage	300V AC/MINUTE
6	D_SUB Operating temperature	-20℃ to 105℃
7	Rated voltage according to	UL:No
8	Rated current according to	UL:No
9	D_SUB Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L200*W95*H55mm /
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2023.04.13			名称	端子台	型号	DB62-G7				
审核						版本	Ver:1.0	客户编号					
核准													
						摄影角度	图版比例	第 1 张 共 1 张					
未注线性公差GB1804-m级 (单位mm)							1:1	中山市肯博电子科技有限公司 www.kingpow.cn					
尺寸	≤3	3-6	6-30	30-120	120-400						400-1000	1000-2000	2000-4000
公差	0.1	0.15	0.2	0.3	0.5						0.8	1.2	2.0
角度公差 ±0.5°													