



项目 Category	参数 Parameter	备注 Comments
板载额定电流 Current	0.8A	
端子接线规格 Terminal	Terminal spacing 5.0mm, wire size 18-26 AWG	
Screw Terminal Size	采用一字螺丝刀, 刀口不能大于2.5mm宽	
D-SUB Material	冲针+环保塑料 RoHS	
PCB Material	FR4	
Voltage	70V maximum between any two sinals	
temperature	-10℃ to 70℃	
Ambient Humidity	10% to 90% RH, NON-CONDENSING	

[illegible]