


PXM6011/03S/ST/0405 Datasheet

Product Name // Inline Cable Connector PXM6011 Series 3
Contact Socket Screw Termination (contacts supplied fitted) 4mm-5mm Cable (Dark Grey Gland) Metal Body No Braid Termination

 [View Product Page](#)



// Product Description:

- | | |
|---|---|
| <ul style="list-style-type: none">Inline Cable ConnectorsWater and dustproof to IP66, IP68, IP69K when mated with compatible connector30 degree push twist locking, tamperproof lock prevents accidental un-matingSocket3 ContactsScrew contacts supplied fitted | <ul style="list-style-type: none">Metal Body No Braid TerminationCable acceptance 4mm-5mm diameterGland Pack PXP6088 available separately to accomodate all sizesPXM6082 Sealing Cap available separately to maintain IP rating of unmated connectorsMate with PXM6010 Series Flex Connectors |
|---|---|

// General Information:

Product Display Title:	Inline Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Approvals:	UL
Body Colour:	Metallic Grey
Body Material:	Brass
Body Material Type:	Metal Body No Braid Termination
Contact Type:	Socket Contact
Coupling Type:	Push-Twist
Current Max:	16A, 11A
Diameter Over Coupling Ring Mm:	32mm
Function:	Inline Cable Connector
Insulation Resistance:	>10 ⁶ MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	5mm
Min Cable Entry Size:	4mm
Max Contact Accomodation Awg:	14AWG
Min Contact Accomodation Awg:	14AWG
Max Contact Accomodation Mm2:	2.5mm2
Min Contact Accomodation Mm2:	2.5mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	3 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-11 Test Ka Salt Mist
Voltage Max:	277V

// Product PDF Links

-  6000 Series power connectors...
-  6000 Series metal body power...

// Product 3D CAD Model Links

-  PXM6011/03S/ST/04053D CAD Model



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)