





端子台：SCSI-50P（CN型接口）

Pin number



parameter table:

Num	Category	Describe
1	Max Current	0.5A
2	Cable gauge (AWG)	18-26 AWG
3	SCSI Pitch:	Pitch:1.27mm
4	PCB Material	FR4
5	SCSI Withstanding voltage	300V AC/MINUTE
6	SCSI Operating temperature	-20℃ to 70℃
7	Rated voltage according to	UL:
8	Rated current according to	UL:
9	SCSI Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L165*W95*H54mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2024.09.25			名称	端子台	型号	SCSI-50P (CN型接口)					
审核														
核准						版本	Ver:1.1	客户编号						
						摄影角度	照纸比例	第 1 张 共 1 张						
未注线性公差GB1804-m级（单位mm）							1:1	中山市肯博电子科技有限公司 www.kingpow.cn						
尺寸	公差	0.1	0.15	0.2	0.3						0.5	0.8	1.2	2.0