


PRODUCT NUMBER

71600-YXXLF



- LEAD FREE, SEE NOTE 6
- TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2
- OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5



NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.




mat'l. code SEE NOTES		surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family 2.54MM IDC	
ltr	ecn no	dr	date	tolerances unless otherwise specified	title	
AP	F12-0046	LMU	12.04.25	angles	QUICKIE III FEM 0.76µm Au	
AR	B-17851	LMU	14.06.05	linear		
				X.X ±0.3	mm	
				X.XX ±0.13	scale 5:1	
				X.XXX ±0.05		
AK	F05-0180	LMU	05.04.22	dr	D.LE	01.01.24
AL	F06-0270	LMU	06.09.12	engr	P.NZ	01.01.24
AM	F06-0274	LMU	06.09.25	chr	JF.N	01.01.24
AN	F09-0233	LMU	09.12.15	appd	P.NZ	01.01.24
sheet	revision	AR	AF			
index	sheet	1	2			

FCJ
sheet 1 of 2
71600
CUSTOMER Drawing


STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64

624
304
204 / 224
004
DASHES NOT AVAILABLE


PLATING
0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF




WITH LATCHING STRAIN RELIEF



LOW PROFILE STRAIN RELIEF



STANDARD STRAIN RELIEF



LATCHING STRAIN RELIEF FOR SLIM HEADER

PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT CENTRAL KEY	STANDARD STRAIN RELIEF	WITHOUT STRAIN RELIEF	LOW PROFILE STRAIN RELIEF	LATCHING STRAIN RELIEF
71600-6YYLF	●					●
71600-3YYLF		●	●			
71600-2YYLF	●				●	
71600-1YYLF	●				●	
71600-0YYLF	●		●			

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406 ISO 1101		mm		QUICKIE	
ltr ecn no dr date		tolerances unless otherwise specified				title			
AF B-17851 LMU 14.06.05		angles linear				IDC RECEPT DR			
AA F10199 GCO 01.04.26						scale N/A			
AB F03019 DLE 03.01.23 dr		D.LE		01.01.24		dwg no		sheet 2 of - size	
AC F05-0180 LMU 05.04.22 engr		P.NZ		01.01.24		71600		A3	
AD F06-0270 LMU 06.09.12 chr		JF.N		01.01.24		type		CUSTOMER Drawing	
AE F06-0274 LMU 06.09.25 appd		P.NZ		01.01.24					
sheet index		revision sheet							

FCI
FCIconnect.com
Copyright FCI