

**Accessories**  
**HDC 10B DC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The protective transportation caps are available for sizes 3, 4, 6 and 8. They can be used with the standard IP65 housings. The easily secured protective transportation caps correspond to protection type IP20 and can be used on all housing bases, the bulkhead and the base housing. A lanyard (not included) can be threaded through the built-in eyelet.

**General ordering data**

|            |                                                    |
|------------|----------------------------------------------------|
| Type       | HDC 10B DC                                         |
| Order No.  | <a href="#">1215910000</a>                         |
| Version    | Heavy-duty connectors, Accessories, Protective cap |
| GTIN (EAN) | 4050118000122                                      |
| Qty.       | 10 pc(s).                                          |

## Accessories

### HDC 10B DC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Length     | 76 mm | Length (inches) | 2.992 inch |
| Width      | 46 mm | Width (inches)  | 1.811 inch |
| Height     | 18 mm | Height (inches) | 0.709 inch |
| Net weight | 9.2 g |                 |            |

### Temperatures

|                             |       |                             |        |
|-----------------------------|-------|-----------------------------|--------|
| Operating temperature, max. | 80 °C | Operating temperature, min. | -20 °C |
|-----------------------------|-------|-----------------------------|--------|

### General data

|                   |                    |          |               |
|-------------------|--------------------|----------|---------------|
| Colour            | white, Transparent | Material | Polypropylene |
| Protection degree | IP20               | Size     | 4             |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 4.0   | EC000437    | ETIM 5.0   | EC000437    |
| ETIM 6.0   | EC002943    | eClass 6.2 | 27-14-34-19 |
| eClass 7.1 | 27-44-02-02 | eClass 8.1 | 27-44-02-02 |
| eClass 9.0 | 27-44-02-92 | eClass 9.1 | 27-44-02-08 |

### Approvals

Approvals



ROHS Conform

### Downloads

|                    |                                                                         |
|--------------------|-------------------------------------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 3 HDC 17/18 EN</a><br><a href="#">FL FIELDWIRING EN</a> |
| Engineering Data   | <a href="#">EPLAN</a>                                                   |

### Accessories HDC 10B DC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

