



Jam Nut Receptacle

TKJB7



Crimp Piggyback

Shell Size	Shell size Code	A Dia. Max.	B Mtg. Flat (Max.)	C* Thread 1.0-6g 0.100 R	D Thread 1.0-6g 0.100 R	E Dia. Max.	F Dia. Max.
11	B	.509 (12.93)	.942 (23.93)	25	15	1.520 (38.6)	.427 (10.85)
13	C	.634 (16.10)	1.066 (27.08)	28	18	1.642 (41.7)	.541 (13.74)
15	D	.759 (19.28)	1.191 (30.26)	31	22	1.768 (44.9)	.666 (16.92)
17	E	.885 (22.48)	1.321 (33.56)	34	25	1.957 (49.7)	.791 (20.09)
19	F	1.009 (25.63)	1.441 (36.61)	38	28	2.035 (51.7)	.880 (22.35)
21	G	1.134 (28.80)	1.566 (39.78)	41	31	2.157 (54.8)	1.005 (25.52)
23	H	1.259 (31.98)	1.691 (42.96)	44	34	2.283 (58.0)	1.130 (28.70)
25	J	1.384 (35.15)	1.816 (46.13)	47	37	2.409 (61.2)	1.255 (31.880)

Dimensions shown in inch (mm)

Specifications and dimensions subject to change

www.ittcannon.com