



General ordering data

Order No.	1971340000
Part designation	SCZ 3.81/05/180F SN SW
Version	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
EAN	4032248681167
Qty.	50 pc(s).

Similar products

Order No.	Part designation	Version
1970910000	SCZ 3.81/02/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1971290000	SCZ 3.81/02/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1971080000	SCZ 3.81/02/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1970920000	SCZ 3.81/03/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1971310000	SCZ 3.81/03/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1971090000	SCZ 3.81/03/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box

1970930000	SCZ 3.81/04/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1971320000	SCZ 3.81/04/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1971110000	SCZ 3.81/04/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1970940000	SCZ 3.81/05/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1971120000	SCZ 3.81/05/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1970960000	SCZ 3.81/06/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1971350000	SCZ 3.81/06/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1971140000	SCZ 3.81/06/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1970970000	SCZ 3.81/07/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1971360000	SCZ 3.81/07/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1971160000	SCZ 3.81/07/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1970980000	SCZ 3.81/08/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1971370000	SCZ 3.81/08/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1971170000	SCZ 3.81/08/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1970990000	SCZ 3.81/09/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1971400000	SCZ 3.81/09/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1971200000	SCZ 3.81/09/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box

1971000000	SCZ 3.81/10/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1971410000	SCZ 3.81/10/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1971210000	SCZ 3.81/10/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1971010000	SCZ 3.81/11/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1971510000	SCZ 3.81/11/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1971220000	SCZ 3.81/11/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1971020000	SCZ 3.81/12/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1971520000	SCZ 3.81/12/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1971230000	SCZ 3.81/12/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1971030000	SCZ 3.81/13/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1971530000	SCZ 3.81/13/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1971240000	SCZ 3.81/13/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1971040000	SCZ 3.81/14/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1971540000	SCZ 3.81/14/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1971250000	SCZ 3.81/14/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1971050000	SCZ 3.81/15/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1971550000	SCZ 3.81/15/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box

1971260000	SCZ 3.81/15/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1971060000	SCZ 3.81/16/180F SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1971560000	SCZ 3.81/16/180F SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1971280000	SCZ 3.81/16/180F SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box