


General information

Part number	A21LOC-P03MPH0-520S
Termination	solder
Size	1
Locking principle	break
Coding	0_key
Cable Diameter	cable_mini_52
Cable outlet	bend_relief




Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.

CODING: 0°



POSITIONS: 3 Positions



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	3
Contact type	pins
Contact diameter	13mm
Insulator material	peek
Wire cross section	20_awg
Termination	solder
Termination diameter	11mm

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	09_mm	11_mm
Nominal current single contact	12_a	iec_60512_5_2
Nominal current insert	12 A	vde_0298_4
Test voltage	15_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip50
Operating temperature	40_120_c
Mating cycles	5000

mated_unmated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text