







NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
COVER: COPPER ALLOYS OR STEEL.
- 2.PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: GOLD OVER NICKEL.
SOLDER AREA: TIN OVER NICKEL.
- 3.MULTIMEDIA CARD COMPATIBLE



 PAD AREA

 KEEP OUT AREA

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05




Circuit Diagram for Detect Switch

WITHOUT CARD	OPEN	
INSERTING CARD	CLOSE	

PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)


TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X:±0.35	X.X':±3°	PART NO. TF-015-N	TITLE: MICRO SD CARD PUSH PUSH SMT 不镀金 无压片 外焊		
X.XX:±0.25	X.XX':±2°				
X.XXX:±0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olivia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



纸箱规格:340*340*322

NO.4



NO.3

1. 材质要求:

- 1.1 纸箱的材质为K=K;外形尺寸为34*34*32.2;
- 1.2 卷盘的材质为PS,卷盘的外形尺寸为 $\phi 330*30.4$;

2. 包装方式:

- 2.1 将卷带放入包装机后,前空5PCS,后放产品1000PCS,再后空5PCS;上带留300MM长度.
- 2.2 将包装好的产品从包装机上取下并包装好,贴上内盘标签;
- 2.3 把累叠好的7盘叠放入纸箱中共计7Kset,上下放纸板;
- 2.4 把包装好的成品打包封箱,并在纸箱外贴上标签

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X:±0.35	X.X':±3"	PART NO. TF-015-N	TITLE: MICRO SD CARD PUSH PUSH SMT 贴片 外焊 包装图	
X.XX:±0.25	X.XX':±2"			
X.XXX:±0.15		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		SCALE N:A
FINISH	---			SHEET 1/1