

## Han 10EMC/B HTE M25 PFT DL



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 810 1121
Specification	Han 10EMC/B HTE M25 PFT DL
HARTING eCatalogue	<a href="https://b2b.harting.com/19628101121">https://b2b.harting.com/19628101121</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> EMC/B
Type of hood/housing	Panel feed through housing
Type	High construction

### Version

Size	10 B
Version	Top entry
Cable entry	1x M25
Locking type	Double locking lever
Han-Easy Lock <sup>®</sup>	Yes
Field of application	Hoods/Housings for higher EMC requirements

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated



**Pushing Performance**  
Since 1945

## Material properties

Colour (hood/housing)	Unpainted
Material (seal)	NBR
Material (locking)	Polycarbonate (PC)
	Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Naphthalene

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	313.9 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140171794
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors