

1 2 3 4 5 6 7 8

Dept

Qty

DC 1

ED 1

IE 1

ISO 1

PD 1

R&D 1

SD 1

QA 1

QC 1

QE 1

晨翔2.54mm牛角，26PIN，弯插，大耳朵，黑胶，四方针镀金，针长15.5/20.5mm

晨翔料号：DS1011-26RBSIB7-B

REV.

DESCRIPTION

DRAWN

CHECKED

APPROVED

A

NEW RELEASE

JLZ 06/29/24'

B

C

D

E

F

G

H

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐压: 600伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

1.4 额定电流: 3安

2. 环境特性:

2.1 工作温度: -40~+105° C

3. 材料:

3.1 端子: H62黄铜, 镍底镀金

3.2 胶芯: PBT, 黑色, 阻燃

52.42±0.5

30.48±0.25

2.54±0.1

0.64

8.4

4.30

7.9

13

17

(28)

2.54

30.48

2.54

ø1.02

2.54

3.70±0.3

PCB孔位尺寸参考

公差: ±0.05

GENERAL TOLERANCE

ANGLE TOLERANCE

PROJECTION

TITLE

2.54mm SHROUDED HEADER

R/A TYPE

UNITS

mm

SHEET SIZE

A4

SERIES

DS1011 SERIES

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1011-XXXXX-A

晨翔电子有限公司

CONNPLY CONNPLY ELECTRONIC CO. LTD