

Han 3EMC-HAE-M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 003 1645
Specification	Han 3EMC-HAE-M25
HARTING eCatalogue	https://b2b.harting.com/19620031645

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Hood

Version

Size	3 A
Version	Side entry
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	80.5 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140171435
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors