

1 2 3 4 5 6 7 8

Dept

Qty

DC

ED

IE

ISO

PD

R&D

SD

QA

QC

QE

晨翔2.54mm牛角，14PIN，弯插，大耳朵，灰胶，四方针镀金

晨翔料号：DS1011-14RBSiA7-B

REV.

A

DESCRIPTION

NEW RELEASE

DRAWN

JLZ 06/28/24'

CHECKED

APPROVED

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐压: 600伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

1.4 额定电流: 3安

2. 环境特性:

2.1 工作温度: -40~+105° C

3. 材料:

3.1 端子: H62黄铜, 镍底镀金

3.2 胶芯: PBT, 灰色, 阻燃

37.18±0.5

15.24±0.25

2.54±0.1

0.64

8.4

4.30

7.9

13.7

17

(28)

2.54

3.70±0.3

15.24

2.54

2.54

φ1.02

PCB孔位尺寸参考

公差: ±0.05

GENERAL TOLERANCE

X. ±0.60

.X ±0.38

.XX ±0.25

ANGLE TOLERANCE

X. ±5°

.X ±3°

.XX ±2°

PROJECTION

UNITS

SHEET SIZE

A4

TITLE

2.54mm SHROUDED HEADER

R/A TYPE

SERIES

DS1011 SERIES

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1011-XXXXX-A

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8