

Han EMC/B 6 Hood Side Entry PG 21



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|--------------------------|------------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han® EMC/B Han® High Temp |
| Type of hood/housing | Hood |
| Type | High construction |

Version

| | |
|----------------------|--|
| Size | 6 B |
| Version | Side entry |
| Cable entry | 1x Pg 21 |
| Locking type | Single locking lever |
| Field of application | Hoods/Housings for higher EMC requirements |

Technical characteristics

| | |
|--|---|
| Limiting temperature | -40 ... +125 °C -40 ... +200 °C With Han® High Temp components |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 IP66 |
| Type rating acc. to UL 50 / UL 50E | 4 12 |

Material properties

| | |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
|-------------------------|--------------------|

Material properties

| | |
|--------------------------------------|---------------|
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 142.24 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140073883 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |