

DO NOT SCALE
FROM THIS PRINT

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:
ONE DECIMALS $\pm .1$ [2.5]	THREE PLACE DECIMALS $\pm .005$ [.13]		
TWO DECIMALS $\pm .01$ [.3]	FOUR PLACE DECIMALS $\pm .002$ [.05]		

TITLE:	.100 x .100 TERMINAL STRIP w/ MOLDED IN END SHROUDS
--------	---

DWG NO:
TSSH-1XX-01-XXX-DH-XX
SHEET 1 OF 2






FIG. 1



SECTION "A-A"
(ROTATED 90°)



NOTES:

1. ~~REF-28~~ REPRESENTS A CRITICAL DIMENSION.
2. SBB SHEET 2 FOR FLUSH SPBCS.
3. MAX FLASH ALLOWED: .010 [.25].
4. PUSHOUT FORCE: 1.5 LB. MINIMUM.
5. NO BANDOLIER MARKS ARE ALLOWED IN THE POST AREA.
6. TUBB PLUG TO BE LOCATED IN THE BODY AREA AND NOT THE TAIL AREA OF THE TUBB.
7. INSULATOR MATERIAL: BLACK, LCP, UL 94 VO






FIG. 2

-A: ALIGNMENT PIN OPTION



PACKAGING TABLE

ROW OPTION	PACKAGING TUBE	PLUG
-DH	PT-1-24-01-44	TP-07



FOR ODD # POSITION FG

$$^{\circ}R = (\text{No OF POS} + 2) \times .100 \quad [2.54]$$

$$^{\circ}\text{S} = \{(^{\circ}\text{R} - .325 [8.26]) / 2\} \pm .020 [.51]$$

FOR EVEN # POSITION FG

$$^{\circ}\text{R} = (\text{No OF POS} + 1) \times .100 \quad [2.54]$$

$$^{\circ}\text{S} = \{(^{\circ}\text{R} - .325 [8.26]) / 2\} \pm .020 [.51]$$

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SANTIC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESS
WRITTEN CONSENT OF SANTIC INC.

FIG. 3

—P: PICK AND PLACE PAD OPTION
(USE PPP-18, 5 POS. MIN)

samtec EMC

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: BURREN 10-10-98

TSSH-1XX-01-XXX-DH-XX
SHEET 1 OF 2