


PAGE 1/1	ISSUE 03-06-13	SERIES LC	PART NUMBER F727711100
----------	----------------	-----------	------------------------



Dimensions: mm [inches]

GENERAL

Type: IEC 61754-20 (LC)
RJ-45 latching system

Mounting: Snap in mounting
Max. panel thickness 1.7mm

Alignment Sleeve: Zirconia

Color: GREEN

CHARACTERISTICS (Dependent on cable or fiber construction)

Material: Plastic molded: Material in accordance with
TELCORDIA GR-326 CORE
Inflammability V0 (UL 94)

Mechanical: Endurance: 200 matings
Plug Retention : 68N

Environmental: Storage temperature range: -40°C / +85°C
Operating temperature range: -40°C / +70°C

Proof Test : Straight pull: 68N
Side pull: 23N

Vibration Test : 10 to 55Hz, 1.5mm (peak to peak), 2Hr/axis

(Performance and specification: see document GEN_F727 001)