



Views from "X"


6-Pole




7-Pole




9-Pole
(8+1)




12-Pole



17-Pole




19-Pole
(16+3)




	Cable Diameter	Solder Contacts	Crimp Contacts
6 Pole	7 – 12mm	KAS6S00-555 1202300002	KAS6S00-405 1202300005
	Crimp range*		0,75-2,5mm ²
7 Pole	7 – 12mm	KAS7S00-555 1202300011	KAS7S00-405 1202300014
	Crimp range*		0,75-2,5mm ²
9 Pole (8+1)	7 – 12mm	KAS9S00-555 1202300020	KAS9S00-425 1202300023
	Crimp range*		0,34-1,0mm ² /0,75-2,5mm ²
12 Pole	3 – 7mm	KASCS00-551 1202300028	KASCS00-021 1202300031
	7 – 12mm	KASCS00-555 1202300029	KASCS00-025 1202300032
	11 – 17mm	KASCS00-559 1202300030	KASCS00-029 1202300033
	Crimp range*		0,34-1,0mm ²
17 Pole	7 – 12mm	---	KASJS00-025 1202300050
	Crimp range*		0,34-1,0mm ²
19 Pole (16+3)	7 – 12mm	---	KASLS00-225 1202300059
	11 – 17mm	KASLS00-559 1202300057	KASLS00-229 1202300060
	Crimp range*		0,34-1,0mm ² /0,56-1,0mm ²


Cable Diameter
3 - 7 mm



Cable Diameter
7 - 12 mm



Cable Diameter
11 - 17 mm



Notes:

Tolerances (unless specified): DIN ISO 2768 m

*Crimp range only applies to "Crimp Contacts" version

FUNCTIONAL SYMBOLS DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#512581.			molex M23 FA CABLE CONNECTOR FEMALE STRAIGHT				
	MM NTS											
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 753973 DRWN: LIKITV 2023/08/17 CHK'D: ANIKES1 2023/08/30 APPR: GGA 2023/08/31			PRODUCT CUSTOMER DRAWING				
		mm	INCH									
	4 PLACES		± ----	± ----	INITIAL REVISION: DRWN: BBRAUCH 2008/11/10 APPR: JKOLB 2009/03/02			DOCUMENT NUMBER SD-120230-001		DOC TYPE PSD	DOC PART 001	REVISION A
	3 PLACES		± ----	± ----								
	2 PLACES		± 0.05	± ----	THIRD ANGLE PROJECTION			MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1
	1 PLACE		± 0.1	± ----								
	0 PLACES		± ----	± ----	A3-SIZE		SERIES 120230					
ANGULAR TOL ± ---- °												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												