

HC-STA-D15-CLWS-1TTM20-EL-AL - Housing



1424359

<https://www.phoenixcontact.com/us/products/1424359>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling housings D15, with single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x M20, height: 52 mm, cable gland: none, Standard

Commercial data

Item number	1424359
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APE
Catalog page	Page 527 (C-2-2019)
GTIN	4055626371016
Weight per piece (including packing)	105.5 g
Weight per piece (excluding packing)	105.5 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-D15-CLWS-1TTM20-EL-AL - Housing



1424359

<https://www.phoenixcontact.com/us/products/1424359>

Technical data

Notes

General	For contact inserts HC-D15, A10
---------	---------------------------------


Product properties

Product type	Housing with locking latch
Housing type	Coupling housings
Product family	HC-STA-D
Application	Standard
Type	D15
No. of cable outlets	1
Type of the screw connection	1x M20
Cable outlet	straight
Pg screw connection	none

Data management status

Article revision	02
------------------	----

Dimensions

Dimensional drawing	
Width	30 mm
Height	52 mm
Length	63.5 mm

Material specifications

Flammability rating according to UL 94	V0 (Interlock)
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Locking latch material	PA

Mechanical properties

Mechanical data

Type of the screw connection	1x M20
Locking type	Latch

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
----------------------	------

HC-STA-D15-CLWS-1TTM20-EL-AL - Housing



1424359

<https://www.phoenixcontact.com/us/products/1424359>

	IP67
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-D15-CLWS-1TTM20-EL-AL - Housing


1424359

<https://www.phoenixcontact.com/us/products/1424359>



Drawings

Dimensional drawing




Dimensional drawing

1424359

<https://www.phoenixcontact.com/us/products/1424359>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424359>




DNV
Approval ID: TAE000037S



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026



cULus Recognized

HC-STA-D15-CLWS-1TTM20-EL-AL - Housing



1424359

<https://www.phoenixcontact.com/us/products/1424359>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-STA-D15-CLWS-1TTM20-EL-AL - Housing



1424359

<https://www.phoenixcontact.com/us/products/1424359>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com