


MS/Standard

MS3108A

90 degree plug



To complete order number, see "how to order" pg. 70.
For solder well data, see page 67.
All lockwire holes are .045 dia. min.

Shell Size	A Thread Class 2B	J $\pm .005$	L Max.	Q Dia. Max.	U Max.	V Thread Class 2A	W	Z $\pm .045$
8S	.5000-28UNEF	.531	.896	.741	.750	.5000-28UNEF	.375	.562
10S	.6250-24NEF	.531	.927	.869	.750	.5000-28UNEF	.375	.562
10SL	.6250-24NEF	.531	.951	.946	.875	.6250-24NEF	.375	.562
12S	.7500-20UNEF	.531	.956	.995	.875	.6250-24NEF	.375	.562
12	.7500-20UNEF	.719	1.143	.995	.875	.6250-24NEF	.375	.812
14S	.8750-20UNEF	.531	1.120	1.123	1.000	.7500-20UNEF	.375	.562
14	.8750-20UNEF	.719	1.207	1.123	1.000	.7500-20UNEF	.375	.812
16S	1.0000-20UNEF	.531	1.146	1.250	1.062	.8750-20UNEF	.375	.562
16	1.0000-20UNEF	.719	1.332	1.250	1.062	.8750-20UNEF	.375	.812
18	1.1250-18NEF	.719	1.395	1.333	1.188	1.0000-20UNEF	.375	.812*
20	1.2500-18NEF	.719	1.645	1.461	1.250	1.1875-18NEF	.375	.812*
22	1.3750-18NEF	.719	1.645	1.588	1.312	1.1875-18NEF	.375	.812*
24	1.5000-18NEF	.719	1.896	1.715	1.438	1.4375-18NEF	.375	.812*
28	1.7500-18NS	.719	1.896	1.968	1.500	1.4375-18NEF	.375	.812*
32	2.0000-18NS	.719	2.118	2.209	1.750	1.7500-18NS	.438	.812*
36	2.2500-16UN	.719	2.176	2.463	1.875	2.0000-18NS	.500	.812*
40	2.5000-16UN	.719	2.301	2.719	2.031	2.2500-16UN	.500	.812*

* Increase Z dimension by .312 for size "0" contact only.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[MS3108A14S-1S](#) [MS3108A18-17S](#) [MS3108A18-20P](#) [MS3108A28-19P](#) [MS3108A28-19S](#) [MS3108A22-22S](#)
[MS3108A14S-1P](#) [MS3108A22-22SX](#) [MS3108A36-52SZ](#) [MS3108A16-13P](#) [MS3108A22-10P](#) [MS3108A22-10S](#)
[MS3108A28-15SW](#) [MS3108A28-11PW](#) [MS3108A22-14PW](#) [MS3108A28-15PW](#) [MS3108A22-22PX](#) [MS3108A28-](#)
[11SX](#) [MS3108A24-28PX](#) [MS3108A28-11SZ](#) [MS3108A18-19SX](#) [MS3108A24-28SZ](#) [MS3108A18-16S](#) [MS3108A22-](#)
[14PX](#) [MS3108A18-16P](#) [MS3108A14S-10P](#) [MS3108A14S-10S](#) [MS3108A28-21PW](#)